



Laboratories



Catering



Factories



Meat  
slaughterhouses

**Ideal** for all types of meats with and without bone: hams, pallets, bacon, jars, knuckles, chickens...

**Suitable** for all types of productions, depending on the model.

**Recommended** for sausage factories, laboratories...

The **SAP** is ideal for:



Meats




Sausages


**We design, manufacture and market.**

Seriousness, commitment, quality and service... loyalty to our customers.


The high level of vacuum, combined with interval massage, causes a thorough exudation of proteins, an opening of tissue cells, and prevents foaming, eliminating cooking waste process of massaging by the friction of the meat against the meat, allows the preservation of the solid texture of the muscle without deteriorating the products.




**SAP-70**




**SAP-200**



**SAP-470**



**SAP-800**



**SAP-1200**

**Features**

- Easy maintenance and cleaning
- Manufacture according to CE standard
- Massage shovel
- Top with airtight closure

**Equipment**

- Digital programmer: CD system
- Speed regulator

**Technical data**

| Model:                  | SAP-70               | SAP-200              | SAP-470              | SAP-800              | SAP-1200             |
|-------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Exterior dimensions/mm: | 1280x600x870         | 1500x700x1470        | 1800x800x1400        | 2580x880x1520        | 2660x1120x1800       |
| Drum volume/Lts:        | 70                   | 200                  | 470                  | 800                  | 1200                 |
| Power/Kw:               | 0,5                  | 0,75                 | 0,75                 | 2                    | 4                    |
| Electrical connection:  | 220/380V 50/60Hz 3ph |
| Pump:                   | 8 m <sup>3</sup> /h  | 21 m <sup>3</sup> /h | 21 m <sup>3</sup> /h | 40 m <sup>3</sup> /h | 63 m <sup>3</sup> /h |
| Weight/kg:              | 97                   | 180                  | 273                  | 425                  | 610                  |

**Information about the digital programmer**

- Cycle programmer:
  - Rotation with and without vacuum
  - Continuous rotation with and without vacuum
- Emergency stop
- Vacuum activation, at will
- Automatic download of the product by reversal of spin, according to model

\*see descriptions on the web